

SILENTA[®]

HEARING PROTECTOR TECHNOLOGY



SILENTeX[®]

COMMUNICATION HEARING PROTECTORS

THE ELECTRONIC HEARING PROTECTOR SERIES IS
A RESULT OF INNOVATIVE DEVELOPMENT WORK
MADE BY THE SILENTA GROUP.

BLUETOOTH PRODUCT LINE



BLUETOOTH PRODUCT LINE



A-COM BT	P/N	Software version	Functions
Silentex A-Com BT	9000310	no	Bluetooth
Silentex A-Com BT Cap	9210310	no	Bluetooth
Silentex A-Com BT NB	9030310	no	Bluetooth
Silentex A-Com BT	9000315	Motorola	Bluetooth
Silentex A-Com BT Cap	9210315	Motorola	Bluetooth
Silentex A-Com BT NB	9030315	Motorola	Bluetooth



NATURAL XPB	P/N	Software version	Functions
Silentex Natural XPB BT A	7000000	no	Bluetooth + Level dependent
Silentex Natural XPB BT A Cap	7010000	no	Bluetooth + Level dependent
Silentex Natural XPB BT A NB	7030000	no	Bluetooth + Level dependent
Silentex Natural XPB BT A	7000005	Motorola	Bluetooth + Level dependent
Silentex Natural XPB BT A Cap	7010005	Motorola	Bluetooth + Level dependent
Silentex Natural XPB BT A NB	7030005	Motorola	Bluetooth + Level dependent



MULTI XPB	P/N	Software version	Functions
Silentex Multi XPB BT A FM	7000200	no	Bluetooth + Level dependent + FM Radio
Silentex Multi XPB BT A FM Cap	7010200	no	Bluetooth + Level dependent + FM Radio
Silentex Multi XPB BT A FM NB	7030200	no	Bluetooth + Level dependent + FM Radio
Silentex Multi XPB BT A FM	7000205	Motorola	Bluetooth + Level dependent + FM Radio
Silentex Multi XPB BT A FM Cap	7010205	Motorola	Bluetooth + Level dependent + FM Radio
Silentex Multi XPB BT A FM NB	7030205	Motorola	Bluetooth + Level dependent + FM Radio



WICOM FM	P/N	Software version	Functions
Silentex WiCom BT FM	5705000		Bluetooth + FM Radio
Silentex WiCom BT FM Cap	5715000		Bluetooth + FM Radio

SILENTA®

PTT / TALK ON SHELL

**ALLOWS TO COMMUNICATE
EFFECTIVELY**

**TO FURTHER
IMPROVE
SAFETY**

**ENABLES
TO FOCUS ON WORK
EVEN UNDER
EXTREME
CONDITIONS**

**EASY TO USE
EVEN WHEN
WEARING
WORK GLOVES**

**TO FURTHER
IMPROVE USER
SATISFACTION**

**MECHANICALLY
RELIABLE**

SILENTA®

SERVICE SUPPORT

The basic maintenance instructions can be found in the user guide. Our service support is reliable and of high quality. For further details, please contact service@silenta.com.

Hygiene Kit: Includes two ear cushions and insulation foams for the earcups. We recommend to replace the cushions as necessary, at least every 6 months in order to guarantee the best performance and hygiene.

Storage: Before and after using ear-muffs store them in a clean dust-free place. After long-term use it is recommended to turn the ear cups outwards to allow the insulation foam to dry.




Hygiene kit Slim line
Art. No 6007000



Hygiene kit High
Attenuation line
Art. No 6008000

BLUETOOTH PRODUCT LINE

HEADBAND	A-Com BT	Natural XPB	Multi XPB	WiCom FM
Foldable headband with comfortable pressure				
SNR	33 dB	33 dB	33 dB	26 dB
NRR	26 dB	26 dB	26 dB	19 dB
HELMET MOUNTED	A-Com BT Cap	Natural XPB Cap	Multi XPB Cap	WiCom FM Cap
Silenta helmet mounting arm and Clip-On adapter system enables attachment to most helmets on the market				
SNR	32 dB	32 dB	32 dB	25 dB
NRR	25 dB	25 dB	25 dB	18 dB
Rechargeable Li-on battery	100 h or 20 h Bluetooth active	60 h or 20 h Bluetooth active	50 h or 20 h Bluetooth active	60 h or 20 h Bluetooth active
QUALIFIED BLUETOOTH DEVICE 				
Bluetooth with A2DP, HFP and HSP profiles	●	●	●	●
Push-To-Talk on shell	●	●	●	●
Easy to connect by simple pairing feature	●	●	●	●
Bluetooth Wireless transmission range 10 m	●	●	●	●
ACTIVE LEVEL DEPENDENT				
User can hear instructions, speech and warning signals from surrounding environment	●	●	●	●
Enables face-to-face communication while hearing is protected	●	●	●	●
FM RADIO				
High quality sound and automatic channel search	●	●	●	●
Max FM volume is limited to 82 dB	●	●	●	●
USER-FRIENDLY AND RELIABLE				
Hermetically sealed electronics and high quality components	●	●	●	●
Ergonomical mic boom with excellent background noise cancellation	●	●	●	●
Rechargeable Li-on battery	●	●	●	●
Low battery warning	●	●	●	●
Automatic switch off after 5 hours	●	●	●	●
Soft and replaceable ear cushions	●	●	●	●
Spacious cups for the maximum user comfort	●	●	●	●
CE-marked, approved in accordance with PPE directive 89/686/EEC	●	●	●	●

SIGMACOM

radiocommunication.ch

Rue de la Dixence 49 – CH-1950 Sion
 T +41 (0)27 322 41 01 F +41 (0)27 322 41 02
 info@sigmacom.ch – www.sigmacom.ch

SILENTA®

Silenta Group Oy • Länsiväylä 7 • 40700 Jyväskylä, Finland

Postal address: Silenta Group Oy • P.O. Box 10 • FI-40701 Jyväskylä, Finland

Telephone +358 14 3771522 • Fax +358 14 3771622

E-mail: silenta@silenta.com • www.silenta.com

